

ACCUTIRE®

# ESCAPE HAMMER & TIRE GAUGE

- Range  
5 to 150 PSI
- White LED  
Flashlight
- Easy to Read  
Large Display
- Metal Safety  
Hammer
- Seat Belt  
Cutter
- Batteries  
included



MODEL MS-4520

ACCUTIRE®

## EXTEND THE LIFE OF YOUR TIRES!

### Specifications

Range: 5-150 PSI

Accuracy: +/- 1% + 0.5 PSI

Operating Temperature: 14°F ~ 122°F (-10°C ~ 50°C)

Power: 3 x AAA Battery (replaceable)

Remove battery tab before 1st use. Open battery cap to remove tab, gauge is now ready for use.

### Measuring Tire Pressure

1. Push nozzle of gauge onto tire valve.
2. Hold gauge on valve stem until the pressure reading is displayed and locked.
3. The pressure reading will show (stay) on the LCD for about 7 seconds. Then gauge will turn off.

### Replacing the Battery

1. Unscrew the battery cap and remove the old battery.
2. Insert new 3 AAA batteries.
3. Replace the battery cap cover and screw it tightly. Check your tire gauge once a week, the battery life is about 3 years based on 5 operations per day.

### Battery notes

1. Do not mix old and new batteries.
2. Do not mix Alkaline, standard (carbon-zinc) or rechargeable (Nickel cadmium) batteries.

### Tire Pressure Advice and Actions

Always be sure to follow the vehicle manufacturer's pressure ratings which are based on cool tire temperatures. Use a soft damp cloth to clean your tire gauge. Do not use any liquids or cleansers.

### Troubleshooting:

1. The display is blank  
Make sure that the pressure seal between the tire gauge and the valve stem is free from leaks.
2. The display reads "0.0" even if pressure applied in correct manner  
The unit has an internal calibration error. Return to factory for service.
3. The unit displays an unusually high/low reading  
Check to make sure there are no leaks in the system or during measurement. Re-zero the unit by taking a reading, and allowing the unit to automatically shut off. Then recheck the tire pressure.

### Warning

This product contains lead, a chemical known to the State of California to cause birth defects and other reproductive harm.

### Warranty and Service

Measurement Ltd., Inc warrants this product against defects in material or workmanship for a period of five (5) years from the date of purchase and agrees to replace it free of charge. This warranty does not cover damage resulting from misuse or abuse of the product. Should your product require service, you may send it back to Measurement Ltd., Inc for repair or replacement.

Our authorized service center address:  
11751 Rock Landing Drive, Suite H-7,  
Newport News, VA 23606  
Attn: Customer Service  
Tel: 757-706-3839



Measurement Ltd., Inc.  
www.measurement-ltd.com



Made in China